

Aircraft Icing and Meteorology Research

Droplet Size, Velocity and Time-of-Arrival

Number Density

Liquid Water Content

Liquid Volume Flux

Built-in DPSS laser for long life and stable operation

Fully heated for cold weather operation (to -40°C)

Dual size range; data automatically merged for extended size range

Single electronics cable with watertight connectors

PDI Dual Range Flight Probe

The PDI Flight Probe has been developed specifically for aircraft-based cloud studies that require the measurement of liquid droplet size distribution, velocity distribution, number density, and liquid water content (LWC). The probe incorporates the well established phase Doppler technique for directly measuring the size and velocity of individual droplets in the cloud. The measurement method is sensitive only to spherical particles and therefore non-spherical ice crystals are rejected. Furthermore, the probe has the ability to differentiate between liquid droplets and droplets that are frozen. The PDI Flight Probe overcomes the inherent problems, such as depth-of-focus, measurement uncertainty, and coincidence errors in high number density environments, faced by older and obsolete measurement technologies which are based on forward light scattering.

The PDI Flight Probe offers turnkey operation with a fully automated setup feature. The flight probe system can be used for the real-time, non -intrusive measurement of individual droplet size and single velocity component in a variety of flight and windtunnel applications. The complete instrument includes the flight probe (including the optical transmitter and receiver), ASA signal processor, and the AIMS system software. The diode-pumped solid state (DPSS) laser used in the probe provides stability, compactness, ruggedness, and high reliability; it eliminates the need for inefficient and unreliable fiber optics. The **PDI-FPDR** system has optional built-in heaters to prevent ice accretion. This allows the flight probe to be used under extreme icing environments without any signal loss.

This probe was developed with funding support from the U.S. Navy, U.S. Army, and NASA Glenn Research Center.



High-precision measurement systems for energy, environmental, and industrial applications

Technical Specifications:

1		(DANGER)	
Size Range	0.5 to 2500 µm	VISIBLE AND/OR INVISIBLE	
Velocity Range	1 to 500 m/s	LASER RADIATION, AVOID DIRECT EXPOSURE TO BEAM	
Size Resolution and Accuracy	+ /- 0.5 μm	CLASS 3b LASER	
Liquid Water Content (LWC)	0 to 50 g/m^3		
LWC Resolution	0.1 g/m^3		
LWC Uncertainty	<10%		
Instrument Weight	~15 kg		
Approximate Dimensions	L = 100 cm, W = 180 cm, H = 180cm		
Power/Voltage	12 – 52 VDC or 120 – 240 VE	C	
Fix Edit Signet Acquisitors Views Scripti Melasok Help			



US Patents: 7, 126, 694 B1, 7, 564, 564 B2, 7, 788, 067 B2, 8, 525, 093 B2 EPO Patent: EP 1 855 081 B1

Our offices, research facilities, and manufacturing plant are located in Sunnyvale, California, where we serve our North American customers. Our distributor partners provide valuable services to our customers in other parts of the world.

CHINA: OPLAN Co. Ltd. oplanchina.com +86-10-62623871	GERMANY: LaVision GmbH lavision.com +49-(0)551-9004-0	INDIA: Tesscorn AeroFluid Inc. <u>tesscorn-aerofluid.com</u> +91.80.2572.9425 59	JAPAN: Seika Digital Image Corporation seika-di.com +81-3-3405-1288	SPAIN: Solma Environmental Solutions sol-ma.net +34608756759
---	--	--	---	--

artium.com | info@artium.com | +1 (408) 737-2364 | Sunnyvale, CA USA